

XBO 75 W/2 OFR

XBO $\leq$ 450 W Double End




Areas of application

- Endoscopy
- Microscopy
- Surgical Headlamps
- Fiber Illumination
- Solar Simulation
- Imaging & Scanning

Product features and benefits

- High luminance / radiance with intense point source
- Color temperature approximately 6000 K (daylight) consistent through the life of the lamp
- High color rendering index: $R_a >$
- High arc stability
- High arc stability
- Hot restart capability
- Dimmable over a wide range
- Long lamp life



Technical data

General Product Information

Product number (Americas)	69232
Product name (Americas)	XBO 75W/2 OFR 14V 10/CS 1/SKU
Family brand	XBO
Lamp type	DOUBLE ENDED
Product remark	OFR = Ozone-free version
Global order reference	XBO 75 W/2 OFR

Electrical Data

Nominal wattage	75 W
Lamp voltage	12...16 V ¹⁾
Lamp current	4.9...5.9 A
Type of current	DC


¹⁾ Initial voltage range

Photometric Data

Nominal luminous flux	1000 lm
Luminous intensity	100 cd ¹⁾
Color temperature	6000 K
Color rendering index Ra	98
Light center length (LCL)	37.0 mm

¹⁾ Typical initial photometric value

Physical Attributes & Dimensions



Electrode gap (cold)	0.9 mm
Base (anode)	SFa9-2
Base (cathode)	SFa7.5-2

Product datasheet

Diameter (in)	39.331 in
Diameter	10.0 mm
Length	90.0 mm
Product weight	11.00 g

Operating Conditions

Burning position	s100 ¹⁾
Cooling	Convection

¹⁾ If vertical, then anode on top; up to 10° below horizontal, cathode on top

Lifetime Data

Nominal lifetime	400 hr
Average life - vertical	400 hr
Average life - horizontal	400 hr

Environmental & Regulatory Information

Information according Art. 33 of EU Regulation (EC) 1907/2006 (REACH)	
Primary article identifier	4050300508825
Declaration no. in SCIP database	536f5044-6629-4551-b556-81347c0c9dfe
Candidate list substance 1	Lead
CAS No. of substance 1	7439-92-1
Safe use instruction	The identification of the Candidate List substance is sufficient to allow safe use of the article.

Country specific information

Product code	METEL code	SEG-No.	STK-Number	UK Org
4050300508825	OSRXBO752OFR	-	-	-

Product datasheet

Safety advice

Because of their high luminance, UV radiation and high internal pressure in both the hot and cold state, XBO lamps must only be operated in appropriate enclosed casings. Always use the protective jackets supplied when handling these lamps. They may only be used as open lamps if appropriate safety measures are taken. More information is available on request or can be found in the leaflet included with the lamp or the operating instructions.

Logistical Data

Product code	Product description	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Volume	Gross weight
4050300508825	XBO 75 W/2 OFR	Folding carton box 1	165 mm x 95 mm x 48 mm	0.77 dm ³	91.00 g
4050300508832	XBO 75 W/2 OFR	Shipping carton box 10	235 mm x 225 mm x 210 mm	11.10 dm ³	1138.00 g

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

Disclaimer

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.